



Archery Needs?
Think Big!

SHIBUYA RECURVE ARROWREST ULTIMA

For many years, top athletes have requested that Shibuya develop an arrow rest tailored to their needs. Finally, Shibuya announces its Ultima Recurve Rest, which has been developed through Shibuya's decades of experience with feedback from champion archers such as Natalia Valeeva and Magnus Petersson!

Every single detail of this product is extremely accurate, in order to guarantee an exceptional performance and comfort of use.


The Ultima Recurve Rest's Support Arm makes use of DLC-coating (Diamond-like carbon) a technology offering superior material strength and friction properties, applied in fields such as parts for racing engines. As a result, the energy loss inflicted on an arrow gliding over the arm is reduced to the bare minimum. The Support Arm's Offset construction guarantees no contact with the cushion plunger's barrel, even when used with the smallest diameter shafts.

The Ultima Recurve Rest is adjustable vertically, to ensure compatibility with any size arrow shaft, and also horizontally to compensate for sight window depth and plunger settings. Adjustments are easy to make with one screw, even when the arrow is rested on the support arm. The Support Arm is available as a spare part on request, and can be replaced easily.

By employing CNC milling, the three-dimensional construction enables the magnets to be arranged in a V-shape groove. The line of magnetic force between the Ultima Recurve Rest's dual magnets secures the support arm in position consistently, exponentially increasing the reliability of the rest.

Shibuya uses only highest quality corrosion-resistant samarium cobalt magnets, known for their constant magnetic force independent of temperature changes.

Just like Shibuya's world-famous sight systems, the Ultima Recurve Rest is produced in Japan to guarantee meticulous quality standards.



The Ultima recurve arrowrest is available in 5 beautiful colors.



Despite the 3mm screw used the ULTIMA arrowrest profile is very small.

By placing the adjustment screw between the magnets, Shibuya was able to maintain a super-slim construction (only 3.8mm including adhesive tape), while at the same time using a 3mm screw for comfortable, safe adjustments.

Ultima Recurve Rest can be switched between RH and LH simply by reversing the support arm's fastening direction.

For attachment to the bow riser, Shibuya is employing industrial-strength double-sided adhesive tape from a trusted maker.

The Plunger cutout is precisely machined to match the diameter of popular cushion plungers, such as Shibuya's DX Plunger. Ultima Recurve Rest is available in six attractive colors (Black, Silver, Blue, Red, Gold and Pink).

The "V"-shape groove that hosts the magnets ensures maximum precision and repeatability



Code 53D529 SHIBUYA RECURVE ARROW REST ULTIMA RH/LH BK/SL/BL/GD/RD/PK